



WBSP1S-MW

Silhouette 10A socket Horz + shutter MW

Technical properties

Configuration

Number of modules	1
-------------------	---

Main electrical features

Nominal voltage	250 V AC
Frequency	50 Hz

Electric current

Rated current	10 A
---------------	------

Dimensions

Insertion depth	23 mm
Height	77 mm
Width	117 mm

Materials

Colour	white
Surface appearance	matt

Installation, mounting

Entries	cable entries bevelled
Mounting type	flush-mounted
Installation mode	for screw fastening

Connection

Type of connection	with screw terminals
--------------------	----------------------

Scope of delivery

Scope of delivery	supplied with standard tapered point 32 mm fixing screws
-------------------	--

Equipment

Number of socket outlets switchable	1
-------------------------------------	---

Safety

IK protection code against mechanical impacts	IK08
RoHS conform	Yes
Protection	Enhanced contact protection

Identification

Main design line	silhouette
------------------	------------