




WBSP2S



Silhouette 10A twin socket Horz+ shutter

Technical properties

Electric current

Rated current	10 A
---------------	------

Frequency

Frequency	50 - 50 Hz
-----------	------------

Voltage

Rated voltage	250 V
---------------	-------

Safety

With enhanced contact protection	Yes
Impact resistance IK	IK08
Ingress Protection (IP) class	IP20

Dimensions

Built-in depth flush-mounted boxes	23 mm
Built-in depth	23 mm
Height	77 mm
Width	117 mm
Depth	33 mm

Materials

Colour	White
Surface finish	Glossy
Material	Polycarbonate (PC), Thermoplastic

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Connectivity

Type of connection	Screw terminal
With claw mounting	No
Mounting type	Screw mounting

Equipment

Connector/plug type socket outlet	Australian standard AS/NZS 3112
Rotated central insert	No
With hinged lid	No
With round protective earth pin	No
With signal lamp	No
With lock	No

Accessories

Has labelling field	No
---------------------	----

Capacity

Number of modules	2
-------------------	---

Texts

Imprint	Without imprint
---------	-----------------

Cover	Full cover plate
-------	------------------

Protection	Enhanced contact protection
------------	-----------------------------

Type of connection	With screw terminals
--------------------	----------------------

Cover, door

Type of lid	Without lid
-------------	-------------

Related Series	silhouette
----------------	------------