




WBSP2S-MW



## SIL. 10A twin socket Horz+ shutter MW

### Technical properties

#### Electric current

Rated current	10 A
---------------	------

#### Frequency

Frequency	50 - 50 Hz
-----------	------------

#### Safety

Impact resistance IK	IK08
Ingress Protection (IP) class	IP20

#### Dimensions

Built-in depth flush-mounted boxes	23 mm
Built-in depth	23 mm
Height	77 mm
Width	117 mm
Depth	33 mm

#### Materials

Colour	White
Surface finish	Matt
Material	Polycarbonate (PC), Thermoplastic

#### Installation, mounting

Mounting on	Flush mounting
-------------	----------------

#### Connectivity

Type of connection	Screw terminal
Mounting type	Screw mounting

#### Equipment

Connector/plug type socket outlet	Australian standard AS/NZS 3112
Rotated central insert	No
With hinged lid	No
With round protective earth pin	No
With signal lamp	No

#### Accessories

Has labelling field	No
---------------------	----

#### Capacity

Number of modules	2
-------------------	---

**Texts**

---

Imprint	Without imprint
Cover	Full cover plate
Protection	Enhanced contact protection
Type of connection	With screw terminals
Related Series	silhouette

---