




WBSSV2-MB



## Silhouette 2G LP Switch Vert MB

### Technical properties

#### Electric current

Rated current 16 A

#### Installation, mounting

Mounting on Flush mounting

#### Frequency

Frequency 50 - 50 Hz

#### Materials

Colour Black

Surface finish Matt

Material Polycarbonate (PC)

Treatment Varnished

#### Identification

Assembly arrangement Basic element with full cover plate

#### Connectivity

Mounting type Screw mounting

#### Controls and indicators

Number of buttons 2

#### Dimensions

Built-in depth 23 mm

#### Safety

Ingress Protection (IP) class IP20

#### Texts

Installation mode For screw fastening

Type of connection With screw terminals

Lighting Without lighting (cannot be illuminated)

Switch mode 2-way, with loop terminal