



WBSSV6

Silhouette 6G LP Switch Vert

Technical properties

Architecture

Type of control unit	rocker
----------------------	--------

Configuration

Antibacterial treatment	No
-------------------------	----

Controls and indicators

Number of buttons	6
-------------------	---

Main electrical features

Nominal voltage	250 V AC
-----------------	----------

Frequency	50 Hz
-----------	-------

Electric current

Rated current	16 AX
---------------	-------

Dimensions

Insertion depth	23 mm
-----------------	-------

Height	117 mm
--------	--------

Width	77 mm
-------	-------

Materials

Colour	white
--------	-------

Installation, mounting

Mounting type	flush-mounted
---------------	---------------

Installation mode	for screw fastening
-------------------	---------------------

Connection

Type of connection	with screw terminals
--------------------	----------------------

Type of connection	Screw connection
--------------------	------------------

Scope of delivery

Scope of delivery	supplied with standard tapered point 32 mm fixing screws
-------------------	--

Safety

RoHS conform	Yes
--------------	-----

Halogen free	Yes
--------------	-----