



WBWP1S

## Socket IP53 single horizontal 10A

### Technical properties

#### Configuration

Number of modules	1
-------------------	---

#### Main electrical features

Nominal voltage	250 V AC
-----------------	----------

#### Electric current

Rated current	10 A
---------------	------

#### Dimensions

Height	85 mm
--------	-------

Width	85 mm
-------	-------

#### Materials

Colour	light grey
--------	------------

Colour	light grey
--------	------------

Material	tempered glass
----------	----------------

Surface appearance	glossy
--------------------	--------

#### Installation, mounting

Mounting type	surface-mounted
---------------	-----------------

#### Connection

Type of connection	with screw terminals
--------------------	----------------------

#### Equipment

Number of socket outlets switchable	1
-------------------------------------	---

#### Safety

IK protection code against mechanical impacts	IK08
---	------

Protection index IP	IP53
---------------------	------

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

Protection	without enhanced contact protection
------------	-------------------------------------

#### Identification

Main design line	Weather protected
------------------	-------------------