



WBWP2S

Socket IP53 twin horizontal 10A

Technical properties

Configuration

Number of modules	2
-------------------	---

Main electrical features

Nominal voltage	250 V AC
-----------------	----------

Electric current

Rated current	10 A
---------------	------

Dimensions

Height	85 mm
--------	-------

Width	115 mm
-------	--------

Materials

Colour	light grey
--------	------------

Colour	light grey
--------	------------

Material	tempered glass
----------	----------------

Surface appearance	glossy
--------------------	--------

Installation, mounting

Mounting type	surface-mounted
---------------	-----------------

Connection

Type of connection	with screw terminals
--------------------	----------------------

Equipment

Number of socket outlets switchable	2
-------------------------------------	---

Safety

IK protection code against mechanical impacts	IK08
---	------

Protection index IP	IP53
---------------------	------

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

Protection	without enhanced contact protection
------------	-------------------------------------

Identification

Main design line	Weather protected
------------------	-------------------