



WBWP2SH

Socket IP53 Twin horizontal 10A Shallow mount

Technical properties

Configuration

| | |
|-------------------|---|
| Number of modules | 2 |
|-------------------|---|

Main electrical features

| | |
|-----------------|----------|
| Nominal voltage | 250 V AC |
|-----------------|----------|

Electric current

| | |
|---------------|------|
| Rated current | 10 A |
|---------------|------|

Dimensions

| | |
|--------|-------|
| Height | 85 mm |
|--------|-------|

| | |
|-------|--------|
| Width | 115 mm |
|-------|--------|

Materials

| | |
|--------|------------|
| Colour | light grey |
|--------|------------|

| | |
|--------|------------|
| Colour | light grey |
|--------|------------|

| | |
|----------|----------------|
| Material | tempered glass |
|----------|----------------|

| | |
|--------------------|--------|
| Surface appearance | glossy |
|--------------------|--------|

Installation, mounting

| | |
|---------------|-----------------|
| Mounting type | surface-mounted |
|---------------|-----------------|

Connection

| | |
|--------------------|----------------------|
| Type of connection | with screw terminals |
|--------------------|----------------------|

Equipment

| | |
|-------------------------------------|---|
| Number of socket outlets switchable | 2 |
|-------------------------------------|---|

Safety

| | |
|---|------|
| IK protection code against mechanical impacts | IK08 |
|---|------|

| | |
|---------------------|------|
| Protection index IP | IP53 |
|---------------------|------|

| | |
|---------------|-----|
| REACH conform | Yes |
|---------------|-----|

| | |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|

| | |
|------------|-------------------------------------|
| Protection | without enhanced contact protection |
|------------|-------------------------------------|

Identification

| | |
|------------------|-------------------|
| Main design line | Weather protected |
|------------------|-------------------|