



WBWS116

## Switch IP66 1 gang 16A

### Technical properties

#### Architecture

Type of control unit	rocker
----------------------	--------

#### Configuration

Antibacterial treatment	No
-------------------------	----

#### Compatibility

IFTTT support available	No
-------------------------	----

#### Controls and indicators

Number of buttons	1
-------------------	---

#### Main electrical features

Nominal voltage	250 V AC
-----------------	----------

#### Electric current

Rated current	16 A
---------------	------

#### Dimensions

Height	85 mm
--------	-------

Width	85 mm
-------	-------

#### Materials

Colour	light grey
--------	------------

Colour	light grey
--------	------------

#### Installation, mounting

Mounting type	surface-mounted
---------------	-----------------

Installation mode	for screw fastening
-------------------	---------------------

#### Connection

Type of connection	Screw connection
--------------------	------------------

#### Safety

Protection index IP	IP66
---------------------	------