



WBWS216



Switch IP66 2 gang 16A

Technical properties

Electric current

| | |
|---------------|------|
| Rated current | 16 A |
|---------------|------|

Installation, mounting

| | |
|-------------|------------------|
| Mounting on | Surface mounting |
|-------------|------------------|

Materials

| | |
|----------------|--------------------|
| Colour | Light grey |
| Surface finish | Glossy |
| Material | Polycarbonate (PC) |

Identification

| | |
|----------------------|-------------------------------------|
| Assembly arrangement | Basic element with complete housing |
|----------------------|-------------------------------------|

Connectivity

| | |
|---------------|----------------|
| Mounting type | Screw mounting |
|---------------|----------------|

Controls and indicators

| | |
|-------------------|---|
| Number of buttons | 2 |
|-------------------|---|

Dimensions

| | |
|----------------|---|
| Built-in depth | 0 |
|----------------|---|

Safety

| | |
|-------------------------------|------|
| Ingress Protection (IP) class | IP66 |
|-------------------------------|------|

Texts

| | |
|-------------------|--|
| Installation mode | For screw fastening |
| Lighting | Without lighting (cannot be illuminated) |
| Switch mode | 2-way, with loop terminal |