



WBWSH4-BK

**IP66 4G Switch 10A H W/Proof Black**

**Technical properties**

**Architecture**

|                      |        |
|----------------------|--------|
| Type of control unit | rocker |
|----------------------|--------|

**Controls and indicators**

|                   |   |
|-------------------|---|
| Number of buttons | 4 |
|-------------------|---|

**Main electrical features**

|                 |          |
|-----------------|----------|
| Nominal voltage | 250 V AC |
|-----------------|----------|

|           |       |
|-----------|-------|
| Frequency | 50 Hz |
|-----------|-------|

**Electric current**

|               |      |
|---------------|------|
| Rated current | 16 A |
|---------------|------|

**Dimensions**

|                 |       |
|-----------------|-------|
| Insertion depth | 25 mm |
|-----------------|-------|

|        |       |
|--------|-------|
| Height | 77 mm |
|--------|-------|

|       |        |
|-------|--------|
| Width | 117 mm |
|-------|--------|

**Materials**

|        |       |
|--------|-------|
| Colour | black |
|--------|-------|

|        |       |
|--------|-------|
| Colour | black |
|--------|-------|

**Installation, mounting**

|               |               |
|---------------|---------------|
| Mounting type | flush-mounted |
|---------------|---------------|

|                   |                     |
|-------------------|---------------------|
| Installation mode | for screw fastening |
|-------------------|---------------------|

**Connection**

|                    |                      |
|--------------------|----------------------|
| Type of connection | with screw terminals |
|--------------------|----------------------|

|                    |                  |
|--------------------|------------------|
| Type of connection | Screw connection |
|--------------------|------------------|

**Scope of delivery**

|                   |  |
|-------------------|--|
| Scope of delivery | supplied with standard tapered point 32 mm fixing screws |
|-------------------|--|

**Safety**

|                     |      |
|---------------------|------|
| Protection index IP | IP66 |
|---------------------|------|

|               |     |
|---------------|-----|
| REACH conform | Yes |
|---------------|-----|

|              |     |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|