



WDW071

**IP20**

## Flush-mounted housing for WDI07x, flush with wall

### Technical properties

#### Architecture

Fixing mode	flush-mounting
-------------	----------------

#### Functions

Touch function	No
----------------	----

#### Connectivity

Connection	RJ45 cable in scope of delivery
------------	---------------------------------

#### Dimensions

Cavity wall opening (W x H x D)	197.7 x 133.6 x 74 mm
---------------------------------	-----------------------

#### Power

Total power loss under IN	0 W
Dissipated energy in cable	0 W

#### Screen

Display	no
---------	----

#### Materials

RAL colour	RAL 7016 - Anthracite grey
Material	Steel
Material family	Metal

#### Installation, mounting

Installation mode	for flush-mounted and hollow-wall mounting, for vertical and horizontal mounting
-------------------	--

#### Equipment

Text field	No
------------	----

#### Safety

Protection index IP	IP20
Protection	with cleaning cover

#### Use conditions

Storage/transport temperature	-20...60 °C
Relative humidity (without condensation)	10...90 %

#### Identification

Main design line	KNX
------------------	-----