

JF412B

400A 12 Way 125A Outgoers Plain

Architecture

| | |
|-------------|------------------|
| Fixing mode | surface-mounting |
|-------------|------------------|

Main electrical features

| | |
|---------------|-------|
| Rated current | 400 A |
|---------------|-------|

Dimensions

| | |
|----------------------------|--------|
| Depth of installed product | 220 mm |
|----------------------------|--------|

| | |
|-----------------------------|---------|
| Height of installed product | 1400 mm |
|-----------------------------|---------|

| | |
|----------------------------|--------|
| Width of installed product | 900 mm |
|----------------------------|--------|

Cover, door

| | |
|----------------------|-------------|
| Type of door closing | Barrel lock |
|----------------------|-------------|

| | |
|--------------|----------|
| Door locking | with key |
|--------------|----------|

| | |
|---------------|----|
| Interlockable | No |
|---------------|----|

Materials

| | |
|--------|-------|
| Colour | beige |
|--------|-------|

| | |
|------------|------------------|
| RAL colour | RAL 1001 - Beige |
|------------|------------------|

Technical characteristics JF412B

| | |
|----------|-------|
| Material | Steel |
|----------|-------|

Equipment

| | |
|---------------------|----|
| Can be accessorized | No |
|---------------------|----|

Standards

| | |
|-------------------------|-----------|
| European directive WEEE | concerned |
|-------------------------|-----------|

Safety

| | |
|---------------------|----------------------|
| Protection index IP | IP30 |
| Protection class | Protection class III |
