

# JF412BG

## 400A 12 Way 125A Outgoers Glazed

### Architecture

Fixing mode	surface-mounting
-------------	------------------

### Main electrical features

Rated current	400 A
---------------	-------

### Dimensions

Depth of installed product	220 mm
----------------------------	--------

Height of installed product	1400 mm
-----------------------------	---------

Width of installed product	900 mm
----------------------------	--------

### Cover, door

Type of door closing	Barrel lock
----------------------	-------------

Door locking	with key
--------------	----------

Interlockable	No
---------------	----

### Materials

Colour	beige
--------	-------

RAL colour	RAL 1001 - Beige
------------	------------------

Technical characteristics JF412BG

---

Material	Steel
----------	-------

---

Equipment

Can be accessorized	No
---------------------	----

---

Standards

European directive WEEE	concerned
-------------------------	-----------

---

Safety

Protection index IP	IP30
Protection class	Protection class III

---