

JF60204BG

630A 6 Way 2*250A + 4*125A Glazed

Architecture

Fixing mode surface-mounting

Main electrical features

Rated current 630 A

Dimensions

Depth of installed product 220 mm

Width of installed product 900 mm

Cover, door

Type of door closing Barrel lock

Door locking with key

Interlockable No

Materials

Colour beige

RAL colour RAL 1001 - Beige

Material Steel

Technical characteristics JF60204BG

Equipment

Can be accessorized No

Standards

European directive WEEE concerned

Safety

Protection index IP IP30

Protection class isol.class I
