

JF80408BG

800A 12 Way 4*250A + 8*125A Glazed

Architecture

Fixing mode	surface-mounting
-------------	------------------

Main electrical features

Rated current	800 A
---------------	-------

Dimensions

Depth of installed product	220 mm
----------------------------	--------

Height of installed product	1400 mm
-----------------------------	---------

Width of installed product	900 mm
----------------------------	--------

Cover, door

Type of door closing	Barrel lock
----------------------	-------------

Door locking	with key
--------------	----------

Interlockable	No
---------------	----

Materials

Colour	beige
--------	-------

RAL colour	RAL 1001 - Beige
------------	------------------

Technical characteristics JF80408BG

RAL colour number	7035
-------------------	------

Material	Steel
----------	-------

Equipment

Can be accessorized	No
---------------------	----

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

Protection index IP	IP30
---------------------	------

Protection class	Protection class III
------------------	----------------------
