



Weekly time switch with reserve 3 modules

Technical Characteristics

Bus system	
Fixing mode	Din-Rail
Bus system radio frequent	No
Frequency	50 Hz
Type of supply voltage	
Supply voltage	230V AC
Breaking capacity	16A 250V AC1
Colour	
RAL colour number	
Max. power fluo. duo lamp comp. series	
Tightening torque	
Mounting type	din-Rail
Connection cross-sect. flexible conductor	1 / 4mm ²
Connection cross-sect. rigid cable	1 / 4mm ²
Type of load	
Type of connection	with screw
Type of contacts	1 changeover
Type of connection	with screw terminals
Summer / Winter time change	manual
Shortest switching time	2 h
Astronomic program	
Type of programming	analog
Programming cycle	1X7D.
Type of display	
Type of programmable thermostat	
Supply failure reserve	200 h
Quick connect	
With holidays program	No
DCF	No

Cycle	weekly
Protection index IP	IP20
Working accuracy	1