



Daily time switch 1 channel, 1 modules with reserve

Technical Characteristics

Fixing mode	Din-Rail
Frequency	50 Hz
Supply voltage	230V AC
Breaking capacity	16A 250V AC1
Mounting type	din-Rail
Connection cross-sect. flexible conductor	1 / 4mm ²
Connection cross-sect. rigid cable	1 / 4mm ²
Type of connection	with screw
Type of contacts	1 changeover
Type of connection	with screw terminals
Summer / Winter time change	manual
Shortest switching time	15 mn
Type of programming	analog
Programming cycle	24H
Type of display	
Supply failure reserve	200 h
With holidays program	No
DCF	No
Cycle	daily
Protection index IP	IP20
Working accuracy	1