

# ET421

## Override contactor 25A 4NO



- Main electrical features
  - Frequency  
50/60 Hz
- Voltage
  - Rated insulation voltage  
400 V
  - Rated impulse withstand voltage  
4 kV
- Electric current
  - Acceptable current rating with AC1  
20 A
- Dimensions
  - Depth of installed product  
61 mm
  - Height of installed product  
85 mm
  - Width of installed product  
35 mm
- Power
  - Total power loss under IN  
5 W
  - Power dissipation per coil  
0.24 W
- Endurance
  - Electric endurance in number of cycles  
30000
  - Number of mechanical operations

1000000

- Capacity
  - Number of modules  
2
- Connection
  - Connection cross-sect. flexible conductor  
1 / 6mm<sup>2</sup>
  - Connection cross-sect. rigid cable  
1,5 / 10mm<sup>2</sup>
  - Type of connection  
with screw
  - Number of contacts  
4
  - Type of contacts  
4NO
- Equipment
  - Can be accessorized  
No
- Standards
  - European directive WEEE  
not concerned
- Use conditions
  - Storage temperature  
-40/80 °C
- Temperature
  - Operating temperature  
-10/50 °C