

ET341

Override contactor 40A 3NO



- Main electrical features
 - Frequency
50/60 Hz
- Voltage
 - Rated insulation voltage
400 V
 - Rated impulse withstand voltage
4 kV
- Electric current
 - Acceptable current rating with AC1
40 A
- Dimensions
 - Depth of installed product
64 mm
 - Height of installed product
85 mm
 - Width of installed product
52.5 mm
- Power
 - Total power loss under IN
10.3 W
 - Power dissipation per coil
0.67 W
- Endurance
 - Electric endurance in number of cycles
30000
 - Number of mechanical operations

1000000

- Capacity
 - Number of modules
3
- Connection
 - Connection cross-sect. flexible conductor
4 / 16mm²
 - Connection cross-sect. rigid cable
4 / 25mm²
 - Type of connection
with screw
 - Number of contacts
3
 - Type of contacts
3NO
- Equipment
 - Can be accessorized
No
- Standards
 - European directive WEEE
not concerned
- Use conditions
 - Storage temperature
-40/80 °C
- Temperature
 - Operating temperature
-10/50 °C