



Hours counter

Technical Characteristics

Fixing mode	Din-Rail
Frequency	50 Hz
Depth of installed product	60 mm
Height of installed product	90 mm
Width of installed product	35 mm
Total power loss under IN	1.5 W
Number of modules	2
Supply voltage	230 V +/- 15%
Mounting type	din-Rail
Connection cross-sect. flexible conductor	1 / 6mm ²
Connection cross-sect. rigid cable	1,5 / 10mm ²
Type of connection	with screw
Protection index IP	IP20
Operating temperature	-10 °C 45 °C