



### IP66 Single 13A Double Pole Switched Socket

#### Technical Characteristics

Fixing mode	surface-mounting
Nominal voltage	250 V
Rated voltage	220 V AC 230 V AC
Rated current	13 A
Rated current	13 A
Depth	88.25 mm
Height	116.5 mm
Width	103 mm
Cover	Full cover plate
Colour	light grey
Material	Polycarbonate (PC)
Surface appearance	glossy
Type of surface treatment	untreated
Colour syntax: Colour	light grey
Imprint	without imprint
Type of connection	screw
Wiring	with earth connection
Protection index IP	IP66
Protection	Enhanced contact protection
Designation syntax: Core designation/function	socket outlet