



### 2 Gang Double Pole Switched Socket with LED Indicator & Back Box with Knockouts

#### Technical Characteristics

Fixing mode	flush-mounting
Nominal voltage	250 V
Rated voltage	220 V AC 230 V AC
Rated current	13 A
Rated current	13 A
Depth	53.2 mm
Height	86 mm
Width	146 mm
Cover	Full cover plate
Colour	grey
Material	Steel
Surface appearance	glossy
Type of surface treatment	Epoxy
Colour syntax: Colour	grey
Imprint	without imprint
Type of connection	screw
Wiring	with double earth connection
Component	with 2 fixing screws M3.5 x 20 mm and M3.5 x 30 mm each
Protection index IP	IP20
Protection	Enhanced contact protection
Designation syntax: Core designation/function	socket outlet