

KXA16L

Feed-through terminal-phase, 16mm², 400V/76A, screw connection



Architecture

Fixing mode on mounting rail according to DIN EN 50022

Main electrical features

Rated current 76 A

Dimensions

Depth of installed product 12 mm

Power

Total power loss under IN 1 W

Dissipated energy in cable 1 W

Materials

Colour stone grey

Material Polyamid (PA)

Connection

Connection cross-sect. flexible conductor 1 ; 16mm²

Connection cross-sect. rigid cable	1,5 ; 25mm ²
Type of connection	with screw
