

WMS51

5A 1 Gang Unswitched Socket



- Architecture
 - Fixing mode
flush-mounting
- Main electrical features
 - Nominal voltage
250 V
 - Rated current
5 A
- Dimensions
 - Depth
25 mm
 - Height
86 mm
 - Width
86 mm
- Frequency
 - Frequency
50/60 Hz
- Cover, door
 - Cover
Full cover plate
- Materials
 - Material
Urea-formaldehyde
 - Surface appearance
glossy
 - Type of surface treatment

- untreated
- Colour syntax: Colour white
- Installation, mounting
 - Imprint without imprint
- Connection
 - Type of connection screw
- Cable
 - Wiring with earth connection
- Scope of delivery
 - Component with 2 fixing screws M3.5 x 30 mm
- Safety
 - Protection index IP IP20
 - Protection Enhanced contact protection
- Identification
 - Designation syntax: Core designation/function socket outlet