

SRA02005

Bar/Cable-through Current Transformer BG 113 200/5A 2,5VA Class 1



- Architecture
 - Fixing mode
Din-Rail or on a fixing plate
- Main electrical features
 - Frequency
50;60 Hz
- Voltage
 - Rated insulation voltage
3 kV
- Dimensions
 - Depth of installed product
30 mm
 - Height of installed product
70 mm
 - Width of installed product
49.5 mm
 - Height of opening
20 mm
- Power
 - Total power loss under IN
2.2 W
- Connection
 - Connection cross-sect. flexible conductor
1,5 ; 6mm²
 - Connection cross-sect. rigid cable
1,5 ; 6mm²
 - Type of connection

screw

- Standards
 - European directive WEEE concerned
- Safety
 - Protection index IP
IP10
- Use conditions
 - Storage temperature
-40/40 °C
- Temperature
 - Operating temperature
-40/40 °C