

SRA02505

Bar/Cable-through Current Transformer BG 113 250/5A 2,5VA Class 1

Architecture

Fixing mode	Din-Rail or on a fixing plate
-------------	-------------------------------

Main electrical features

Frequency	50;60 Hz
-----------	----------

Voltage

Rated insulation voltage	3 kV
--------------------------	------

Dimensions

Depth of installed product	30 mm
----------------------------	-------

Height of installed product	70 mm
-----------------------------	-------

Width of installed product	49.5 mm
----------------------------	---------

Height of opening	20 mm
-------------------	-------

Power

Total power loss under IN	2.6 W
---------------------------	-------

Connection

Connection cross-sect. flexible conductor	1,5 ; 6mm ²
Connection cross-sect. rigid cable	1,5 ; 6mm ²
Type of connection	screw
Standards	
European directive WEEE	concerned
Safety	
Protection index IP	IP10
Use conditions	
Storage temperature	-40/40 °C
Temperature	
Operating temperature	-40/40 °C