

WRCC50NBSW

45A Cooker Control Unit Brushed Steel White Insert



Architecture

Fixing mode flush-mounting

Main electrical features

Nominal voltage 250 V

Rated voltage 220/230 V AC

Rated current 45 A

Rated current 45 A

Dimensions

Depth 39.6 mm

Height 86 mm

Width 146 mm

Frequency

Frequency 50;60 Hz

Capacity

Number of modules 0

Technical characteristics WRCC50NBSW-A

Cover, door

Cover	Full cover plate
-------	------------------

Materials

Colour	stainless steel optics
--------	------------------------

Material	stainless steel
----------	-----------------

Surface appearance	matt
--------------------	------

Type of surface treatment	brushed
---------------------------	---------

Colour syntax: Colour	stainless steel
-----------------------	-----------------

Installation, mounting

Imprint	without imprint
---------	-----------------

Connection

Type of connection	Screw connection
--------------------	------------------

Cable

Wiring	with double earth connection
--------	------------------------------

Scope of delivery

Component	with 2 fixing screws M3.5 x 30 mm
-----------	-----------------------------------

Safety

Protection index IP	IP20
---------------------	------

Protection	to protect downstream loads
------------	-----------------------------

Use conditions

Insert	insert white
--------	--------------
