

52205

:hager

- Main electrical features
 - Frequency
50 Hz
- Power supply
 - Supply voltage
8 V AC (by transformer 230 V / 8 V)
- Detection
 - Detection angle
90 °
- Materials
 - Colour
white
- Installation, mounting
 - Mounting type
surface-mounted
- Settings
 - Response value sensitivity adjustable
No
- Safety
 - Protection index IP
IP20
- Temperature
 - Operating temperature
0/45 °C