

# Product data sheet

EEK525P

**:hager**



## Pluggable Digital PIR Occupancy Sensor 5 meter lead

### Technical Characteristics

Fixing mode	flush-mounting
Frequency	50/60 Hz
Breaking capacity	16A 250V AC1
Supply voltage	230 V +10% / -15%
Detection angle	360 °
Colour	white
Brightness measurement range	1000 Lux 5 Lux
Maximum Mounting Height	3.5 m
Type of load	24 DALI/ DSI ballasts
Time delayed range	1min to 1h
Response value sensitivity adjustable	No
Remote controllable	EEK001, EEK002
Protection index IP	IP41
Protection class	isol.class II