



Motion detector infrared 360°, IP55, wall mounted, white

Technical Characteristics

Fixing mode	surface-mounting
Function	can be used as a single unit, main device or extension unit
Frequency	50/60 Hz
Height of installed product	2.5 m
Dimensions (W x H x D)	139 mm 91 mm 153 mm
Max. power with fluo uncompensated lamps	400 W
Incandescent bulb power	1500 W
Breaking capacity	AC1
Supply voltage	230 V +10% / -15%
Detection angle	360 °
Colour	white
Brightness measurement range	1000 Lux 5 Lux
Mounting type	surface-mounted
Maximum Mounting Height	4 m
Connection type	quick connect
Type of contacts	1W + neutral
Type of connection	with screw terminals
Time delayed range	5s ; 15min
Setting	with potentiometers for fine adjustment of the response brightness, sensitivity and delay time
Response value sensitivity adjustable	Yes
Component	with fitting material
Protection index IP	IP55
Operating temperature	-20 °C 55 °C
Application, usage	Motion detector