

VSR916CU

Design 50,16Way,High Integrity,100A Switch,2*100A 30mA RCCB



- Architecture
 - Fixing mode
surface-mounting
- Main electrical features
 - Frequency
50 Hz
 - Rated current
100 A
- Dimensions
 - Depth of installed product
105 mm
 - Height of installed product
284 mm
 - Width of installed product
539 mm
- Capacity
 - Number of modules
16
- Cover, door
 - Type of door closing
non keylock
 - Interlockable
Yes
- Materials
 - Colour
RAL 9010
 - RAL colour number

- 9010
 - Material
Steel
- Equipment
 - Number of rows
1
 - Can be accessorized
Yes
- Standards
 - European directive WEEE
concerned
- Safety
 - Protection index IP
IP2XC