

# VSR912CU

Design 50,12Way,High Integrity,100A Switch,2\*100A 30mA RCCB



- Architecture
  - Fixing mode  
surface-mounting
- Main electrical features
  - Frequency  
50 Hz
  - Rated current  
100 A
- Dimensions
  - Depth of installed product  
105 mm
  - Height of installed product  
284 mm
  - Width of installed product  
467 mm
- Capacity
  - Number of modules  
12
- Cover, door
  - Type of door closing  
non keylock
  - Interlockable  
Yes
- Materials
  - Colour  
RAL 9010
  - RAL colour number

- 9010
  - Material  
Steel
- Equipment
  - Number of rows  
1
  - Can be accessorized  
Yes
- Standards
  - European directive WEEE  
concerned
- Safety
  - Protection index IP  
IP2XC