

VSR810C

Design 50, 10 Way Split Load Configurable, 100A Switch 2*80A 30mA RCCB



- Architecture
 - Fixing mode
flush-mounting
- Main electrical features
 - Rated current
100 A
- Dimensions
 - Depth of installed product
105 mm
 - Height of installed product
284 mm
 - Width of installed product
431 mm
- Cover, door
 - Interlockable
Yes
- Materials
 - Material
Steel
- Equipment
 - Can be accessorized
Yes
- Standards
 - European directive WEEE
concerned
- Safety
 - Protection index IP

