

Product data sheet

VMLA90910H

:hager



Dual Row 100A Sw, 2*100A 30mA RCCB, 9+10 Way, 2 pole busbar, ARC Fault

Technical Characteristics

Fixing mode	surface-mounting
Frequency	50 Hz
Rated current	100 A
Depth of installed product	100 mm
Height of installed product	486 mm
Width of installed product	478 mm
Number of modules	19
Type of door closing	non keylock
Interlockable	No
Colour	white
Colour	white
RAL colour	RAL 9010 - Pure white
RAL colour number	9010
Material	Steel
Number of rows	2
Can be accessorized	Yes
European directive WEEE	concerned
Protection index IP	IP2XC
Protection class	isol.class II