

VML24H

Consumer unit, Design 10, 2way, garage, 40A, 30mA, RCCB, 32A MCB and 6A MCB



- Architecture
 - Fixing mode
surface-mounting
- Main electrical features
 - Rated current
40 A
- Dimensions
 - Depth of installed product
98.2 mm
 - Height of installed product
245 mm
 - Width of installed product
154 mm
- Capacity
 - Number of modules
2
- Cover, door
 - Type of door closing
non keylock
 - Interlockable
Yes
- Materials
 - Colour
pure white
 - RAL colour number
9010
 - Material

Steel

- Equipment
 - Number of rows
1
 - Can be accessorized
No
- Standards
 - European directive WEEE
concerned
- Safety
 - Protection index IP
IP2XC
 - Protection class
Protection class III