

VM966TGSPD

10 Way 100A 100mA Time Delay + 2 x 100A RCCB Type 2 SPD



- Architecture
 - Fixing mode
surface-mounting
- Main electrical features
 - Rated current
100 A
- Dimensions
 - Depth of installed product
102.5 mm
 - Height of installed product
240 mm
 - Width of installed product
400 mm
- Cover, door
 - Interlockable
Yes
- Materials
 - Colour
pure white
 - RAL colour
RAL 9010 - Pure white
 - RAL colour number
9010
 - Material
Steel
- Equipment
 - Number of rows

1

- Can be accessorized
Yes
- Standards
 - European directive WEEE concerned
- Safety
 - Protection index IP
IP2XC