

# VM916CK

16 Way Conf 100A Switch 2\*100A 30mA RCCB with Knockouts



- Architecture
  - Fixing mode  
surface-mounting
- Main electrical features
  - Rated current  
100 A
- Dimensions
  - Depth of installed product  
102 mm
  - Height of installed product  
240 mm
  - Width of installed product  
471 mm
- Capacity
  - Number of modules  
16
- Cover, door
  - Type of door closing  
non keylock
  - Interlockable  
Yes
- Materials
  - RAL colour number  
9010
  - Material  
Steel
- Equipment

- Number of rows  
1
- Can be accessorized  
Yes
- Standards
  - European directive WEEE  
concerned
- Safety
  - Protection index IP  
IP2XC