

VM914CUKSPD

Design 30 , 14 way Configureable HI 100A Sw 2*100A 30mA RCCB Type A KO



- Architecture
 - Fixing mode
surface-mounting
- Main electrical features
 - Rated current
100 A
- Dimensions
 - Depth of installed product
102.5 mm
 - Height of installed product
240 mm
 - Width of installed product
472 mm
- Cover, door
 - Interlockable
Yes
- Materials
 - Colour
pure white
 - RAL colour
RAL 9010 - Pure white
 - RAL colour number
9010
 - Material
Steel
- Equipment
 - Number of rows

1

- Can be accessorized
Yes
- Standards
 - European directive WEEE concerned
- Safety
 - Protection index IP
IP2XC