



Dual Row, 10+14 Way Hi Integrity 100A Switch 2*100A 30mA Type RCCB Type 2 SPD

Technical Characteristics

Fixing mode	surface-mounting
Rated operational voltage Ue	230 V
Frequency	50 Hz
Rated current	100 A
Depth of installed product	102.5 mm
Height of installed product	480 mm
Width of installed product	364 mm
Number of modules	24
Type of door closing	non keylock
Interlockable	No
Colour	pure white
Colour	white
RAL colour	RAL 9010 - Pure white
RAL colour number	9010
Material	Steel
Number of rows	2
Can be accessorized	Yes
European directive WEEE	concerned
Protection index IP	IP2XC