

VM90810CUK

Dual Row HI Conf 8+10 Way 100A Switch 2*100A RCCB with Knockouts



- Architecture
 - Fixing mode
surface-mounting
- Main electrical features
 - Rated current
100 A
- Dimensions
 - Depth of installed product
105 mm
 - Height of installed product
480 mm
 - Width of installed product
292 mm
- Capacity
 - Number of modules
18
- Cover, door
 - Type of door closing
non keylock
 - Interlockable
Yes
- Materials
 - RAL colour number
9010
 - Material
Steel
- Equipment

- Number of rows
2
- Can be accessorized
Yes
- Standards
 - European directive WEEE
concerned
- Safety
 - Protection index IP
IP2X