

# VM878RK

Consumer unit, Design30, 16way, hi integ, config, 100A sw, 2\*80A, 30mA, RCCB+6A RCBO, KO



- Architecture
  - Fixing mode  
surface-mounting
- Main electrical features
  - Rated current  
100 A
- Dimensions
  - Depth of installed product  
102 mm
  - Height of installed product  
240 mm
  - Width of installed product  
471 mm
- Cover, door
  - Interlockable  
Yes
- Materials
  - Material  
Steel
- Equipment
  - Can be accessorized  
No
- Standards
  - European directive WEEE  
concerned
- Safety

- Protection index IP  
IP2XC