

Product data sheet

VM866HK

:hager



**Consumer unit, Design30, 12way, split load 6+6, 100A
Sw, 2*80A, 30mA, RCCB, KO**

Technical Characteristics

Fixing mode	surface-mounting
Rated current	100 A
Depth of installed product	102 mm
Height of installed product	240 mm
Width of installed product	400 mm
Number of modules	12
Type of door closing	non keylock
Interlockable	Yes
RAL colour number	9010
Material	Steel
Number of rows	1
Can be accessorized	No
European directive WEEE	concerned
Protection index IP	IP2X