

VM816CU

Consumer unit, Design30, 16way, hi integ, config, 100A Sw, 2*80A, 30mA, RCCB



- Architecture
 - Fixing mode
surface-mounting
- Main electrical features
 - Rated current
100 A
- Dimensions
 - Depth of installed product
102 mm
 - Height of installed product
240 mm
 - Width of installed product
471 mm
- Capacity
 - Number of modules
16
- Cover, door
 - Type of door closing
non keylock
 - Interlockable
Yes
- Materials
 - RAL colour number
7035
 - Material
Steel
- Equipment

- Number of rows
1
- Can be accessorized
No
- Standards
 - European directive WEEE
concerned
- Safety
 - Protection index IP
IP2XC