

ESC125

Contactor 25A, 1NO, 230V~50Hz



- Main electrical features
 - Rated operational voltage U_e
230 V
 - Frequency
50 Hz
 - Rated current
25 A
- Voltage
 - Rated insulation voltage
250 V
 - Rated impulse withstand voltage
4 kV
- Dimensions
 - Depth of installed product
60 mm
 - Height of installed product
83 mm
 - Width of installed product
17.85 mm
- Power
 - Total power loss under IN
4.4 W
 - Power dissipation per coil
2.9 W
- Endurance
 - Electric endurance in number of cycles
30000

- Number of mechanical operations
100000
- Capacity
 - Number of modules
1
- Fluorescent bulbs control
 - Max. power with fluorescent parallel lamps
810 VA
- Incandescent bulbs control
 - Max. power with incandescent lamps
1900 W
- Installation, mounting
 - Tightening torque
1,2Nm
- Connection
 - Connection cross-sect. flexible conductor
1 ; 6mm²
 - Connection cross-sect. rigid cable
1 ; 10mm²
 - Type of connection
with screw
 - Type of contacts
1NO
- Equipment
 - Can be accessorized
Yes
- Standards
 - European directive WEEE
concerned
- Safety
 - Protection index IP
2
- Use conditions
 - Storage temperature
-40/80 °C
- Temperature
 - Operating temperature
-10/50 °C