

# Product data sheet

VM610CUK

**:hager**

**:hager**

## **10 Way Hi Integrity Configurable 63A Switch 2\*63A 30mA Type A RCCB with knockout**

### Technical Characteristics

Fixing mode	surface-mounting
Depth of installed product	102.5 mm
Height of installed product	240 mm
Width of installed product	364 mm
Interlockable	No
Can be accessorized	No
European directive WEEE	concerned