

Product data sheet

VM61014CUKSPD

:hager



Dual Row, 10+14 Way Hi Integrity 63A Switch 2*63A 30mA RCCB Type 2 SPD

Technical Characteristics

Fixing mode	surface-mounting
Rated current	63 A
Depth of installed product	102.5 mm
Height of installed product	480 mm
Width of installed product	364 mm
Interlockable	No
Colour	pure white
Colour	white
RAL colour	RAL 9010 - Pure white
RAL colour number	9010
Material	Steel
Number of rows	2
Can be accessorized	Yes
European directive WEEE	concerned
Protection index IP	IP2XC