



Consumer unit, Design30, 2way, 40A, garage board, RCCB, 32A MCB and 6A MCB, KO

Technical Characteristics

Fixing mode	surface-mounting
Rated current	40 A
Depth of installed product	102 mm
Height of installed product	240 mm
Width of installed product	149 mm
Number of modules	2
Type of door closing	non keylock
Interlockable	Yes
RAL colour number	9010
Material	Steel
Number of rows	1
Can be accessorized	No
European directive WEEE	concerned
Protection index IP	IP2XC