



### 10AX 6 Gang 2 Way Wall Switch

#### Technical Characteristics

Switch mode	2 way
Rated current	10 A
Depth	24 mm
Height	86 mm
Width	86 mm
Colour	white
Material	Urea-formaldehyde
Imprint	with clear terminal markings
Terminal	unique patented loop terminal allows neutral looping at the switch
Component	with 2 fixing screws M3.5 x 30 mm
Lighting	without lighting (cannot be illuminated)
Standard	BS EN 60669-1