



Auxiliary contact 6A, 1NO+1NC

Technical Characteristics

Rated operational voltage Ue	230 V
Rated current	6 A
Rated insulation voltage	240 V
Rated impulse withstand voltage	4 kV
Acceptable current rating with AC1	6 A
Depth of installed product	60 mm
Height of installed product	83 mm
Width of installed product	11 mm
Total power loss under IN	0.1 W
Electric endurance in number of cycles	30000
Number of mechanical operations	1000000
Number of modules	0.5
Connection cross-sect. flexible conductor	1 / 6mm ²
Connection cross-sect. rigid cable	1 / 6mm ²
Type of connection	with screw
Number of contacts	2
Type of contacts	1NC+1NO
Can be accessorized	No
European directive WEEE	concerned
Protection class	isol.class II